

PIG® Wheeled Overpack Salvage Drum

PAK710 Storage Capacity 95 gal., UN1H2/X113/S, Thickness .25"

6" polyolefin wheels make it easy to take these 95-gallon, FDA-Compliant overpack salvage drums right to the spill. Perfect for leaking drums up to 55 gallons.

- X-rated for Packing Groups I, II and III, so it's ideal for regulated packaging applications, including shipping hazardous materials by land, sea or rail
- Built-in handle and 6" olefin wheels make it easy to transport right to your shipping vehicle
- Polyethylene material with UV inhibitors is durable, light-weight and chemical-resistant
- Empty containers are nestable to save storage space
- Designed and proven to withstand shipping abuse to keep hazardous materials contained
- Integrated ledges molded into container let you move overpack with a forklift
- Leakproof, twist-on lid is notched so you can easily tighten it with a 2x4 or pole
- Specifically designed and sized for leaking drums up to 55 gallons
- Made from FDA-Compliant resins for containment of food and cosmetic products



Item#	Description	Dimensions	Weight
PAK710-WH		ext. dia. 31.4" x 47.5" H	56 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK710-WH		ext. dia. 80cm x 121cm H	25.4 kg

Specifications

Dimensions	ext. dia. 31.4" x 47.5" H
Storage Capacity	95 gal.
Brand	PIG
Bung Type	No Bung Holes
Drum Type	Poly Drum
Interior Dimensions	24.75" Dia. x 38.5" H
Lid Type	Open-Head - Screw-Top
Lining	Unlined
Thickness	.25"

Sold as	1 each
Weight	56 lbs.
# per Pallet	2
Composition	Polyethylene
UNSPSC	24112109
Pigalog® Page Number	Page 299

Metric Equivalent

Storage Capacity	359.6 L
Weight	25.4 kg
Dimensions	ext. dia. 80cm x 121cm H

Technical Information

Certifications, Approvals and Ratings

Meets FDA requirements, UN1H2/X113/S

Technical Documents

[LDPE Products](#)

[Instructions for Overpack Containers](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com