

Encon® Gravity-Fed Portable Eye Wash Station

PLS724 Portable, Holds 14 gal., Flow Rate 0.4 gal./Minute Minimum

Low-profile, gravity-fed eye wash provides full ANSI flow while extending only 9.5" from the wall.

- Eye wash unit has a 14-gallon capacity, but extends only 9.5" from wall when retractable tray is not in use
- Pinch-valve design and pivoting tray activate unit and ensure flow within one second
- Steady flow rate of 0.4 gpm for 15 minutes meets requirements of ANSI Z358.1
- Separate 5-minute fill line meets requirements for personal eye wash
- Rugged handles make unit easy to carry to outdoor work sites
- Bright-yellow color for instant identification and high visibility
- Use included Hydrosep Additive to keep water fresh
- Wall-mount bracket included



Encon

Specifications

Style	Portable
Dimensions	9.5" W x 20" L x 26" H
Brand	Encon
Capacity	14 gal.
Dispensing Method	Gravity-fed
Flow Rate	0.4 gal./Minute Minimum
Color	Yellow
Fluid Storage Method	Tank
Sold as	1 each
Weight	18.25 lbs.
# per Pallet	18
Composition	Polyethylene
Includes	1 - J-Hook Style Mounting Bracket 1 - 8 oz. Hydrosep® Water Treatment Additive (PLS726) 1 - Eyewash Station

UNSPSC

46181810

Metric Equivalent

Weight	8.3 kg
Dimensions	24cm W x 51cm L x 66cm H

Technical Information

CountryShipOnly

This product can ONLY be shipped to: United States, Australia, Canada, Great Britain, Kuwait, Qatar, United Arab Emirates.

Certifications, Approvals and Ratings

ANSI Z358.1-2014

Technical Documents

Hydrosep® Additive

29 CFR 1910.151(c)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com