

PIG® Plug-N-Seal® No-Freeze Patching Paste

PTY237 For Fuel Tanks, Steel Drums & Containers, 3.25" x 1.75", 1 each

Temporarily stop leaks in cold temperatures that would freeze standard patching pastes.

- Specially formulated for storage and application in cold temperatures that would freeze standard patching pastes
- Temporarily stops leaks until system can be drained or leak source contained
- Excellent chemical resistance makes it ideal for flammable or hazardous leaks
- No preparation needed, even on dirty or rusty surfaces
- Temporarily stops leaks from 2 minutes up to 2 hours
- Ready to use without mixing



Specifications

Style	Drum Patch
Use With	Fuel Tanks, Steel Drums & Containers
Dimensions	ext. dia. 3.25" x 1.75" H
Brand	PIG
Repair Type	Temporary
Temperature Limit	5°F (-15°C) to 150°F (66°C)
Color	Gray/Green
Volume	.75 lb. Container
Sold as	1 each
Weight	.75 lbs.
Composition	Bentonite Clay & Propylene glycol w/ Polymer Base
Shelf Life	2 years
UNSPSC	47131903

Metric Equivalent

Weight	.3 kg
Dimensions	ext. dia. 8.3cm x 4.4cm H

Technical Information



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com