

N2A4 Manifold Gauge



Precision • Impact-Resistant

Accurate

- Precision pressure gauge with Class 1.0 accuracy

Impact-Resistant

- Impact-resistant design
- Durable rubber cover

Aluminum Body with 1/4 Turn Ball Valve Handle

- Reliable, efficient and durable
- Better work experience

Folding Hook

- Hidden hook design, easy to transport

4-Refrigerants for Wider Applications

- Φ 3-1/8 large dial for easy reading
- Commonly used refrigerants on outer rings for better reading

Model	N2A4	
Refrigerant Type	R-22, R-404A, R-134a, R-410A	
Gauge Diameter	in	Φ 3-1/8
Pressure Range	psi	-30 inHg to 800 psi -30 inHg to 500 psi
Hose	No	
Accessory	Carry Case	

1-YEAR WARRANTY