



Empowering you to work smarter

N2D4H Manifold Gauge with Digital Display



Precision • Impact-Resistant

Accurate

- Class 0.4 accuracy
- Over 100% improvement vs. analog gauges

Folding Hook

- Hidden hook design, easy to transport

Aluminum Body with 1/4 Turn Ball Valve Handle

- Reliable, efficient and durable
- Better work experience

Digital Display

- Easy to read
- Auto power off

Impact-Resistant

- Impact-resistant design
- Durable rubber cover

22 Programmed Refrigerant Types

Model		N2D4H	
Refrigerant Type		R-22, R-32, R-134A, R-290, R-404A, R-407A, R-407C, R-410A, R-426A, R-427A, R-434A, R-442A, R-448A, R-449A, R-450A, R-452A, R-453A, R-507A, R-513A, R-600A, R-744, R-1234YF	
Pressure Range	psi	-30 inHg to 720 psi	
Hose	in	Red	1/4" - 1/4"
		Yellow	1/4" - 1/4"
		Blue	1/4" - 1/4"
Standard Length	ft	3x5'	
Accessory		Carry Case	

1-YEAR WARRANTY

www.navacglobal.com