

## N4A4H 4-Valve Manifold Gauge

# 4 Valve



## Precision • Impact-Resistant

### Accurate

- Precision pressure gauge with Class 1.0 accuracy

### Impact-Resistant

- Impact-resistant design
- Durable rubber cover

### Aluminum Body with 1/4 Turn Ball Valve Handle

- Reliable, efficient and durable
- Better work experience

### Folding Hook

- Hidden hook design, easy to transport

### 4-Refrigerants for Wider Applications

- $\Phi$ 3-1/8 large dial for easy reading
- Commonly used refrigerants on outer rings

### 4 Valve

- Easy to use

Model	N4A4H		
Refrigerant Type		R-22, R-404A, R-134a, R-410A	
Gauge Diameter	in	$\Phi$ 3-1/8	
Pressure Range	psi	-30 inHg to 800 psi -30 inHg to 500 psi	
Hose	in	Black 3/8" - 3/8" Red 1/4" - 1/4" Yellow 1/4" - 1/4" Blue 1/4" - 1/4"	
Hose Length	ft	4x5'	
Accessory		Carry Case	

**1-YEAR WARRANTY**