



Empowering you to work smarter

# NMC1 Digital Clamp Meter

NAVAC NMC1 Digital Clamp Meter has a high-precision smart chip for a quick and accurate measurement of electrical current. Its adjustable 1-1/8" jaw makes it easy to get around large conductors. Easy to read with a large backlit LCD. The compact design is ideal for tight spaces.

Leading Technology, Superior Quality, Best Experience.

**Empowering You to Work Smarter**



## Simple • Solid

### High Precision Chip

- Precise measurement

### Backlit LCD

- Easy to read large display

### 1-1/8" Jaw

- Suitable for large conductors

### Compact Design

- Ideal for tight spaces

<b>Model</b>	<b>NMC1</b>
Max Measurement Voltage	600V
Max Measurement AC Current	400 A
Max Measurement Capacitance	4000 µF
Temperature Measurement Range	-40°F~1832°F (-40°C~1000°C)
Weight	9.6 oz
Accessory	Test Leads, Type K Temperature Probe, Storage Bag

**1-YEAR WARRANTY**

www.navacglobal.com