
Quick Guide Manual

What's including:



1 Product 2 Inner trayx1pc

3 Mist generator x2pcs (extra 1pc for stand by)



4 Planting tray x2pcs



5 Plating Tray Cloth x2pcs



6 Power x1pc * Hang up power cable *1pc



6 Absorbent Cloth x30pcs (for Succulent)



8 Remote controller x 1pc




9 Water Spray 100ml x 1pc




10 Cleaning Sponge x1pc


Step 1 Rotate to remove the top cover(Fig1), take off spray head(Fig2),take off planting tray(Fig3)



Step 2 Fill in water up to water level line




Step 3 Install the planting tray, install the Mist generator, and install the upper cover



Step 4 Press "Mode" button for required planting mode-待提供



Step 5 Plug 6 Adapter and push mode on, start for reading



https://www.opcomfarm.com/greenheart/MicroGrowDomeGarden

Please visit OPCOM Farm web site videos of Unboxing,Planting and Cleaning video in detail.

Push Button Operation

Function	Light	Status	Time(On/Off)	LED	PUMP	Fan
Power	●	Moss (Mixed/ Moss-RH Middle)	Power on then into moss growth mode	On 12H/ Off 12H	32 cycles/ day (15mins/ cycle)	FAN ON when LED ON
	●	Herb (Mixed/ Moss-RH Low)		On 9H/Off 15H	12 cycles/ day (15mins/ cycle)	FAN ON when LED ON
	●	Succulent		On 12H/Off 12H	Off	FAN ON when LED OFF
	○	Off	Off	Off	Off	Fan: Off

Limited Warranty

OPCOM Farm Indoor Hydroponic Gardening Systems

What Is Covered:

OpcomLink USA ("OpcomLink") warrants to the original retail purchaser that the OpcomLink product covered by this limited warranty statement,If purchased and operated only in the purchased country, will be free due to defects on repairs and materials for a period of one (1) year from the date of original purchase; in European Economic Area (EEA), the limited warranty is valid for a period of 2 years. For warranty service, you must provide proof of the date of original purchase.

What You Need To Do:

We will not provide any warranty coverage unless your claim is in compliance with all terms of this limited warranty statement and you follow proper return procedure. To request warranty service please call OpcomLink Customer Service at (714) 617-4885 (USA) for warranty repair instructions and return authorization. Once we determine that a repair or replacement is required, you will be asked for your name, address, phone number, e-mail and product serial number and then issued a Return Order Number to use when returning product. Product you return to us must be properly packaged in its original packaging (or packaging providing the product with protection equivalent to the original packaging) and shipped, with the shipping charges prepaid via a shipping method that provides for tracking of your package, to the address provided when you received your Return Order Number.

What OpcomLink Will Do:

If we authorize you to return your product to us or an authorized service provider, OpcomLink will repair or replace your product without charge with a functionally equivalent replacement product. OpcomLink may replace your product with a product that was previously used, repaired and tested to meet OpcomLink specifications. OpcomLink will pay to ship the replacement product to you. By sending product for replacement, you agree to transfer ownership of the original product to OpcomLink. OpcomLink may not return your original product to you. OpcomLink warrants that repaired or replaced products are covered for the greater of either the remainder of the original product warranty or 90 days.

What This Limited Warranty Does Not Cover:

This warranty covers only normal use in the United States and Canada. This warranty is not transferable. This warranty does not cover third party parts or components added to the OpcomLink product after its shipment from OpcomLink. OpcomLink is not responsible for warranty service should the OpcomLink label or logo or the rating label or serial number be removed or should the product fail to be properly maintained or fail to function properly as a result of misuse, abuse, improper installation, neglect, improper shipping, damage caused by disasters such as fire, flood, and lightning, improper electrical current, or service other than by an OpcomLink Authorized Servicer. If a claimed defect cannot be identified or reproduced, you will be held responsible for the costs incurred.

DISCLAIMER OF WARRANTIES:

THE WARRANTY AND REMEDY PROVIDED ABOVE ARE EXCLUSIVE AND IN LIEU OF ALL OTHER EXPRESSED OR IMPLIED WARRANTIES INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE AND NONINFRINGEMENT. UNLESS STATED HEREIN, ANY STATEMENTS OR REPRESENTATION MADE BY ANY OTHER PERSON OR FIRM ARE VOID.

Remedies:

Your exclusive remedy and OpcomLink's entire liability for a material breach of this Agreement will be limited to a refund of the price paid for the OpcomLink products covered by this Agreement. Any action for breach of warranty must be brought within 3 months of the expiration date of the warranty. OpcomLink is not liable for performance delays or for nonperformance due to causes beyond its reasonable control. Except as provided in this written warranty, neither OpcomLink nor its affiliates shall be liable for any loss, inconvenience, or damage, including direct, special, incidental or consequential damages, including lost profits, cost of substitute equipment, downtime, claims of third parties, including customers, or injury to property, resulting from the use or inability to use the OpcomLink products, whether resulting from a breach of warranty or any other legal theory. Some jurisdictions do not allow limits on warranties or remedies for breach in certain transactions. In such jurisdictions, the limits in this paragraph and the preceding paragraph may not apply. In Canada, warranties include both warranties and conditions.

Arbitration, Governing Laws:

Any disputes arising out of this Agreement will be settled by arbitration, before a single arbitrator to be conducted in Los Angeles, California, in accordance with the commercial Arbitration Rules of the American Arbitration Association, and judgment upon the award rendered by the arbitrator may be entered in any court having jurisdiction thereof. This Agreement shall be construed in accordance with the laws of the State of California, except this arbitration clause which shall be construed in accordance with the Federal Arbitration Act.

For additional information, visit our website at:**www.opcomfarm.com**