

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400142-009

Nealy

The Nealy Collection nine-light chandelier offers classic charm with an edge of modern luxury. Curving details are complemented by luxurious white silk shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite straps and completed with K9 glass over brass-tone candle holders.

- Brass-infused glass accents punctuate the sinuous mixed-metal curves of Nealy's collection
- With our without white silk shades, the two-tiered nine-light chandelier adds modern-luxury flair to your room
- Ideal for a tall foyers and entries, formal living rooms, dining rooms or luxe master bedrooms
- With its jewelry-like styling, it's well-suited for Modern and Luxe interiors
- Classic Brushed Nickel Finish frame with Graphite detailing
- Measures 36in diameter x 37 1/2in height
- Uses nine, 60-watt max. candelabra base bulbs or LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel Construction

Glass/Shade: White Silk Shades



Diameter: 36"
Height: 37-1/2"
Overall Ht. W/Chain: 159-1/2"

Width: 5-1/2"
Height: 5-5/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling mounted</p> <p>Mounting center lock-up for outlet box included</p> <p>Ten feet of 9 gauge chain supplied</p> <p>Canopy covers a standard 4" octagonal recessed outlet box</p> <p>5" W., 0.75" ht., 5" depth</p>	<p>Pre-wired</p> <p>15 feet of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Nine 60w max. Candelabra Base</p> <p>E12 base phenolic sockets</p>	<p>cULus Dry location listed</p> <p>1 year warranty</p>