

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P400183-009

Tobin

A modern take on a classic object, Tobin's inspiration comes from the timeless mid-century forms. The tubular arms of the nine-light chandelier extend outward and are made to form a gentle curve that showcase an etched white glass shade and finished in Brushed Nickel. The Tobin collection is ideal for those who appreciate Modern design styles.

- A modern take on a classic form - tubular arms for a gentle curve
- Etched white glass shades punctuate the sleek metallic fittings on the two-tiered nine-light chandelier
- Looks sharp in tall foyers and entries, modern dining rooms, living rooms and family rooms
- Clean fittings and etched white glass shades make Tobin ideal for Modern interiors
- Sleek Brushed Nickel finish
- Measures 32in diameter x 18 5/8in ht.
- Uses nine 100-watt max. medium base bulbs or LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Diameter: 32"
Height: 18-5/8"
Overall Ht. W/Chain: 78-1/2"

Width: 5"
Height: 5-1/4"

Category: Chandeliers

Finish: Brushed Nickel (plated)

Construction: Steel Construction

Glass/Shade: Etched White glass Shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six links of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.875" W., 0.875" ht., 4.875" depth	Pre-wired 15 feet of wire supplied 120 V	Quantity: Nine 100w max. Medium Base E26 base porcelain sockets	cULus Dry location listed 1 year warranty