

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P500139-020

Kempsey

The Kempsey three-light pendant's simple, cylindrical silhouette outlined by Antique Bronze arms makes it a perfect guest for casting light upon a dining table or kitchen island in transitional or farmhouse interiors. A warm, Harvest Linen shade takes center stage as it stylishly disguises the light bulbs within.

- Perfect for hanging individually or in multiples of two or more over a dining table or kitchen island
- Updated, classic styling is ideal for transitional and farmhouse interiors
- A three-light pendant with curved-corner metal frame extends on the outside to capture the textured linen shade within its arms
- Textured linen shade glows from the inside out
- Finished in Antique Bronze with a warm, Harvest Linen shade
- The diffuser elegantly hides the lightbulbs while providing soft, comfortable light
- Uses three 60-watt medium base bulbs, or the LED equivalents, that are sold separately
- Measures 17-3/4 in diameter X 21-3/8 in height, Overall height with stem is 87-1/2 in, wire 120 in
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Pendants

Finish: Antique Bronze (Painted)

Construction: Steel Construction

Glass/Shade: Harvest Linen shade fabric Flat Round



Diameter: 17-3/4"
Height: 21-3/8"
Overall Ht. W/Chain And Stem: 87-1/2"

Glass
Width: 15"
Length: 0-1/8"
Height: 15"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain mounted Mounting plate for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 4.875" W., 1" ht., 4.875" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 60w max. Medium Base E26 base Porcelain sockets	cULus Dry location listed