

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

ⓑ

NOTES: 1. FOR USE WITH PANDUIT, MSW38T15-CR4 & MSW38T15-CR6
CONTINUOUS STRAPPING.

2. APPLICATION TOOL: BT2MS75, BT2HT




3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

4. UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:

.XX = ±.02 [.5]

.XXX = ±.010 [.25]

5. MATERIAL: 304 OR 316 STAINLESS STEEL



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01042
03A	10/08	JAMB	SKB	JJB	ORIG CAD FILE SPEC WAS S41147_03. NOTE 2: APPLICATION TOOL BT1HT REPLACED BY BT2HT	-----
03	10/04	JAMB	EJD	JJB	Ⓒ STRAPPING PART NO'S. IN TITLE BLOCK CHANGED TO BUCKLE PART NO'S. DUE TO A TYPING ERROR	12067
02	9/04	JAMB	EJD	JJB	ⓑ VOIDED PART NO'S. MS375X15-TSR & MS375X15-TSR316 & REPLACED BY PART NO'S. MSW38T15-CR4 & MSW38T15-CR6 ON NOTE 1	12052
01	3/04	BRH	EJD	JJB	Ⓐ CHANGED TO .42", WAS .43"	11500
00	9/03	BRH	EJD	JJB	DRAWING RELEASED	11154

TITLE
.375 in [9.52] ENHANCED METAL STRAPPING BUCKLE
Ⓒ MSBW38-C4 & MSBW38-C6

CUSTOMER DRAWING

ITEM REVISION NAME

N41147BS/04

DATASET FILE NAME

N41147BS_DC/04A


UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .1 [2.54]

.XXX ± .005 [.127]

.XX ± .01 [.25]

ANGLES ± 5 °



THIRD ANGLE
PROJECTION

MATERIAL:

SEE NOTES

DRAWING NUMBER:

N41147BS_DC

DRAWN BY

DATE

CHK

SCALE

BRH

9/03

EJD

2:1

SHT 1 OF 1

SIZE

A