
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOMINAL DUCT SIZE (W)	"A" LENGTH/TOLERANCE INCH [mm]	"B" LENGTH/TOLERANCE MM [inch]	"C" WIDTH INCH [mm]	"TC" THICKNESS INCH [mm]	"HC" HEIGHT INCH [mm]
.5	72.00 ±.18 [1828.8 ±4.5]	N/A	.69 [17.5]	.040 [1.0]	.230 [5.8]
.75		N/A	.94 [23.9]	.050 [1.3]	.240 [6.1]
1		2000.00 ±4.5 [78.74 ±.18]	1.25 [31.8]	.060 [1.5]	.350 [8.9]
1.5			1.75 [44.5]		
2			2.25 [57.2]		
2.5		N/A	2.75 [69.9]		
3		2000.00 ±4.5 [78.74 ±.18]	3.25 [82.6]	.065 [1.6]	.370 [9.4]
4			4.25 [108.0]		
6		N/A	6.25 [158.8]	.080 [2.0]	



NOTES:
1. SEE www.panduit.com FOR COLOR AND PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX.
2. DIMENSIONS IN BRACKETS ARE METRIC EQUIVLENT [mm] or [inch].

PART NO. SYSTEM
COVER EXAMPLE
C 2 LG 2
TYPE
WIDTH (inch)
COLOR
LENGTH (FT) or (M)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	09-20-16	JBN	MRJS	RGRO	RELEASED TO PRODUCTION	D34078CB-DC

TITLE
WIRING DUCT COVER TYPE "C" FOR DUCT TYPES D, F, FS, G AND FIBER DUCT
CUSTOMER DRAWING

ITEM REVISION NAME: D34078CB/04
DATASET FILE NAME: D34078CB_DC/00A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ±
.XX ± ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: POLYVINYL CHLORIDE

DRAWING NUMBER: D34078CB-DC

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
JBN	09-20-16	MRJS	NONE		A