

4458

LED Vanity

Features

Housing

Die-formed Cold-rolled Steel

Finish Option: -30 Oil Rubbed Bronze, -62 Satin Nickel, -05 Black, -06 White, -09 Silver

Optical

Shade: Clear Glass

LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

Electrical

120V

Lamp

E26 LED Bulb (ST21) x 3, 2700K

Certification

ETL/cETL Listed, Damp Rated

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	Lamp	Lumen (TYP)	Finish	Dimension (L X H X E)	Energy Star
4458-3-05-3E26	120V	3 x 8W	ST21, 2700K	2400	Black / Clear Glass	24.8" x 10.9" x 6.3"	---