

C1112D C1116D C1120D C1120D-PD

Ceiling Fixture & Pendant

Features

Housing

Die-formed Cold-rolled Steel
 Finish Option: -08 Gray, -30 Oil Rubbed Bronze, -05 Black
 Pendant Mount by Hanging cable

Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity
 LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light

Electrical

High Power Factor, Low THD
 Bi-level Lighting and Emergency Backup Model Available

Lamp

LED Type: Built-in (Color Temperature Option – 3000K, 4000K)
 Multiple Color Temperature (MCT, 3000K/35000K/4000K) Option Available

Certifications

ETL/cETL Listed, Damp Locations Rated, Energy Star Listed

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	CRI	Lumen (Typ) / CT	Finish	Shade	Dimension (OD X H)	Energy Star
C1112D-30-xxxxK	120V ~ 277V	21W	> 80	1260 / 3000K or 4000K	Oil Rubbed Bronze	Acrylic	11.8" x 2.8"	Yes
C1116D-30-xxxxK	120V ~ 277V	34W	> 80	1980 / 3000K or 4000K	Oil Rubbed Bronze	Acrylic	15.8" x 2.8"	Yes
C1120D-30-xxxxK	120V ~ 277V	44W	> 80	2330 / 3000K or 4000K	Oil Rubbed Bronze	Acrylic	19.7" x 2.8"	Yes

Pendant / LED Type

Model	Input Voltage	Input Wattage	CRI	Lumen (Typ) / CT	Finish	Shade	Dimension (OD X H1 x H)	Energy Star
C1120D-PD-30-xxxxK	120V ~ 277V	44W	> 80	2330 / 3000K or 4000K	Oil Rubbed Bronze	Acrylic	19.7" x 2.8" x 6.0'	Yes