FL0324D-VT FL0339D-VT FL0354D-VT

Vanity

Features

Housing
Aluminum Extrusion with Die-Form Cold-Rolled Steel Ends
Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

Optical
Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity
LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

Electrical
High Power Factor, Low THD

Lamp
LED Type: Built-in (Color Temperature Option – 3000K, 3500K, 4000K, 5000K)

Certification
ETL/cETL Listed for Damp Locations, Energy Star

Warranty
5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	LED CT / CRI	Lumen (TYP)	Finish	Dimension (L x H x E)	Energy Star
FL0324D-VT-xxxxK	120V ~ 277V	11W	3000K / >80	935	Satin Nickel	22.0" x 4.8" x 3.8"	Yes
FL0339D-VT-xxxxK	120V ~ 277V	18W	4000K / >80	1530	Satin Nickel	34.0" x 4.8" x 3.8"	Yes
FL0354D-VT-xxxxK	120V ~ 277V	23W	3000K / >80	1950	Satin Nickel	46.0" x 4.8" x 3.8"	Yes