

# FL5324D-JA8 FL5339D-JA8

## Vanity, CEC Listed

### Features

#### Housing

Die-formed Cold-rolled Steel  
 Finish Option: -62 Satin Nickel, -30 Oil Rubbed Bronze, -06 White

#### Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity

#### Electrical

LED Driver: 120V Triac Dimming Type  
 Min. Dimming Level: 3%  
 High Power Factor ( > 0.98), Low THD ( < 10%)

#### Lamp


LED Type: Built-in (Color Temperature Option – 3000K, 4000K)  
 LM80, TM21 : 60,000 hours Rating  
 LED Rated Life: > 36000 hours  
 LED CRI > 90 per JA8 Standard  
 Flicker Free: Meets JA10 Standard

#### Certifications

ETL/cETL Listed, Energy Star, CEC Listed

#### Warranty

5 Years Warranty on Driver and LED Module



### LED Type

Model	Input Voltage	Input Wattage	LED CT / CRI	Lumen (TYP)	CRI	Finish	Dimension (L x H X E)	Energy Star
FL5324D-3000K JA8	120V	18W	3000K	1327	>90	Satin Nickel	23.5" x 4.8" x 4.5"	Yes
FL5339D-3000K JA8	120V	25W	3000K	2000	>90	Satin Nickel	37.5" x 4.8" x 4.5"	Yes