

FL5324D-E FL5339D-E FL5354D-E

LED Vanity

Features

Housing

Die-formed Cold-rolled Steel

Finish Option: -30 Oil Rubbed Bronze, - 62 Satin Nickel, -05 Black, -06 White, -09 Silver

Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity

LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

Electrical

High Power Factor, Low THD

Lamp

LED Module: Multiple Color Temperature Type (MCT, Adjustable, 3000K/3500K/4000K)

Certification

ETL/cETL Listed, Damp Rated

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	LED CT	CRI	Lumen (TYP)	Finish	Shade	Dimension (L X H X E)
FL5324D-E-MCT-62	120V – 277V	18W	3000K/3500K/4000K	>80	1740	Satin Nickel	Acrylic	25.8" x 4.4" x 4.1"
FL5339D-E-MCT-62	120V – 277V	24W	3000K/3500K/4000K	>80	2300	Satin Nickel	Acrylic	37.6" x 4.4" x 4.1"
FL5354D-E-MCT-62	120V – 277V	36W	3000K/3500K/4000K	>80	3450	Satin Nickel	Acrylic	49.4" x 4.4" x 4.1"