

FL5324D-J-MCT FL5339D-J-MCT FL5354D-J-MCT

LED Vanity

Features Housing Die-formed Cold-rolled Steel Finish Option: - 30 Oil Rubbed Bronze, - 62 Satin Nickel, -05 Black, -06 White, -09 Silver Optical Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light. Electrical High Power Factor, Low THD Lamp LED Module: Multiple Color Temperature Type (MCT, Adjustable, 3000K/3500K/4000K) Certification ETL/cETL Listed, Damp Rated, CEC Listed (Title 24) Warranty 5 Years Warranty on Driver and LED Module	
---	---

LED Type

Model	Input Voltage	Input Wattage	LED CT	Lumen (TYP)	Finish	Shade	Dimension (L X H X E)	CEC Listed
FL5324D-J-MCT-62	120V – 277V	17W	3000K/3500K/4000K	1580	Satin Nickel	Acrylic	22.0" x 4.7" x 2.7"	Yes
FL5339D-J-MCT-62	120V – 277V	23W	3000K/3500K/4000K	2600	Satin Nickel	Acrylic	34.0" x 4.7" x 2.7"	---
FL5354D-J-MCT-62	120V – 277V	35W	3000K/3500K/4000K	3500	Satin Nickel	Acrylic	46.0" x 4.7" x 2.7"	---