

FL5524D-F-MCT FL5539D-F-MCT

LED Vanity

Features

Housing

Die-formed Cold-rolled Steel

Finish Option: - 30 Oil Rubbed Bronze, - 62 Satin Nickel

Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity

LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

Electrical

High Power Factor, Low THD

Lamp


LED Module: Multiple Color Temperature Type (MCT, 3000K, 3500K, 4000K)

Certification

ETL/cETL Listed, Damp Rated

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	LED CT	CRI	Lumen (TYP)	Finish	Dimension (L X H X E)	Energy Star
FL5524D-F-MCT-62	120V – 277V	17W	3000K, 3500K, 4000K	>80	1520	Satin Nickel	24.8" x 5.8" x 3.2"	---
FL5539D-F-MCT-62	120V – 277V	24W	3000K, 3500K, 4000K	>80	2110	Satin Nickel	36.8" x 5.8" x 3.2"	---