

FL5524 FL5539 FL5554

Vanity

Features

Housing

Die-formed Cold-rolled Steel
 Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity
 LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

Electrical

High Power Factor, Low THD

Lamp


LED Type: Built-in (Color Temperature Option – 3000K, 3500K, 4000K, 5000K)
 MCT Type: Adjustable Multiple Color Temperature (3000K, 3500K, 4000K)
 Fluorescent Type: T5 HO Lamp

Certification

UL/cUL, ETL/cETL Listed, Suitable for Damp Locations

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	LED CT / CRI	Lumen (TYP)	Finish	Dimension (L x H x E)	Energy Star
FL5524D-xxxxK	120V	17W	3000K / 80	1520	Satin Nickel	25.5" x 4.8" x 4.0"	Yes
FL5539D-xxxxK	120V ~ 277V	24W	3000K / 80	2110	Satin Nickel	37.5" x 4.8" x 4.0"	Yes
FL5554D-xxxxK	120V ~ 277V	36W	3000K / 80	3220	Satin Nickel	49.3" x 4.8" x 4.0"	Yes
FL5524D-MCT	120V ~ 277V	17W	3000K / 80	1520	Satin Nickel	25.5" x 4.8" x 4.0"	Yes
FL5539D-MCT	120V ~ 277V	24W	3000K / 80	2110	Satin Nickel	37.5" x 4.8" x 4.0"	Yes
FL5554D-MCT	120V ~ 277V	36W	3000K / 80	3220	Satin Nickel	49.3" x 4.8" x 4.0"	Yes

LED Type, High Lumen

Model	Input Voltage	Input Wattage	LED CT	CRI	Lumen (TYP)	Finish	Dimension (L x H x E)	Energy Star
FL5524D-HO-62	120V ~ 277V	25W	3000K or 4000K	80	2000	Satin Nickel	25.5" x 4.8" x 4.0"	---
FL5539D-HO-62	120V ~ 277V	31W	3000K or 4000K	80	2580	Satin Nickel	37.5" x 4.8" x 4.0"	---

T5 HO Lamp Type

Model	Input Voltage	Input Wattage	Finish	Shade	Lamp	Dimension (L x H x E)
FL5524	120V ~ 277V	24W	Satin Nickel	Acrylic	1 x F24T5HO, 24W	25.5" x 4.8" x 4.0"
FL5539	120V ~ 277V	39W	Satin Nickel	Acrylic	1 x F39T5HO, 39W	37.5" x 4.8" x 4.0"
FL5554	120V ~ 277V	54W	Satin Nickel	Acrylic	1 x F54T5HO, 54W	49.3" x 4.8" x 4.0"