

FL5724D FL5736D FL5748D

LED Vanity

Features

Housing

Die-formed Cold-rolled Steel

Finish Option: - 30 Oil Rubbed Bronze, - 62 Satin Nickel

Optical

Shade: High Transmission Acrylic Create Excellent Light Distribution and Uniformity

LED: High Efficiency, High CRI, Binned and Mixed to Reach Uniform Light.

Electrical

High Power Factor, Low THD

Lamp


LED Type: Built-in Multiple Color Temperature (MCT, 3000K, 3500K, 4000K)

Certification

ETL/cETL Listed

Warranty

5 Years Warranty on Driver and LED Module



LED Type

Model	Input Voltage	Input Wattage	LED CT / CRI	Lumen (TYP)	Finish	Dimension (L X H X E)	Energy Star
FL5724D-MCT	120V – 277V	17W	3000K / >80	1450	Oil Rubbed Bronze	24.0" x 4.8" x 3.8"	Yes
FL5736D-MCT	120V – 277V	24W	3000K / >80	2100	Oil Rubbed Bronze	36.0" x 4.8" x 3.8"	Yes
FL5748D-MCT	120V – 277V	36W	3000K / >80	3300	Oil Rubbed Bronze	48.0" x 4.8" x 3.8"	Yes