

# P035-1

## Mini Pendant

### Features

#### Housing

Cold-rolled Steel

Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

#### Optical

Shade: Opal Glass

#### Electrical


120V

#### Lamp

E26 LED Bulb: 9W, Energy Star Listed, Color Temperature, 3000K, 4000K

#### Certification

UL/cUL Listed



### CFL Type

Model	Input Voltage	Finish	Shade	Dimension (OD x H xH1)	Lamp	Energy Star
P035-1-62	120V	Satin Nickel	Opal Glass	4.8" x 8.7" x 31.0"	9W LED Bulb	---

Note: H1- Hanging Cable Length