

P058-1

Mini Pendant

Features

Housing

Cold-rolled Steel

Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

Optical

Shade: Opal Glass

Electrical

120V

Lamp

E26 LED Bulb: 9W, Energy Star Listed, Color Temperature, 3000K, 4000K

Certification

UL/cUL Listed



CFL Type

Model	Input Voltage	Finish	Shade	Dimension (OD x H x H1)	Lamp	Energy Star
P058-1-62	120V	Satin Nickel	Opal Glass	3.5" x 8.5" x 6.0'	9W LED Bulb or 13W CFL	---

Note: H1- Hanging Cable Length