

# P117-1

## Mini Pendant

### Features

#### Housing

Cold-rolled Steel

Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

#### Optical

Shade: Opal Glass

#### Electrical


120V

#### Lamp

E26 LED Bulb: 9W, Energy Star Listed, Dimmable, Omini Direction Type, Color Temperature, 3000K, 4000K

#### Certification

UL/cUL Listed



### LED & CFL Type

Model	Input Voltage	Finish	Shade	Dimension (OD x H x H1)	Lamp	Energy Star
P117-1-62	120V	Satin Nickel	Opal Glass	4.8" x 9.8" x 42.0"	9W LED Bulb, E26	---

Note: H1- Total Height