

P117-3

Mini Pendant

Features

Housing

Cold-rolled Steel

Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

Optical

Shade: Opal Glass

Electrical


120V

Lamp

E26 LED Bulb: 9W, Energy Star Listed, Dimmable, Omini Direction Type, Color Temperature, 3000K, 4000K

Certification

UL/cUL Listed



LED & CFL Type

Model	Input Voltage	Finish	Shade	Dimension (OD x H x H1)	Lamp	Energy Star
P117-3-62	120V	Satin Nickel	Opal Glass	11.0" x 9.8" x 6'	3 x 9W LED Bulb, E26	---

Note: H1- Hanging Cord Length