

# P117-A-3

## Mini Pendant

### Features

#### Housing

Cold-rolled Steel  
 Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

#### Optical

Shade: Clear Glass

#### Electrical


120V

#### Lamp

E26 Filament Type LED Bulb: 8W, Energy Star Listed, Dimmable, Omini Direction Type, Color Temperature 2700K

#### Certification

UL/cUL Listed



### LED Type

Model	Input Voltage	Finish	Shade	Dimension (OD x H x H1)	Lamp	Energy Star
P117-A-3-62	120V	Satin Nickel	Clear Glass	11.0" x 9.8" x 6'	3 x E26 Filament Type LED Bulb, 8W, 2700K	---

Note: H1-Hanging Cord Length