

P117-A

Mini Pendant

Features

Housing

Cold-rolled Steel
 Finish Option: -62 Satin Nickel -30 Oil Rubbed Bronze

Optical

Shade: Clear Glass

Electrical


120V

Lamp

E26 Filament Type LED Bulb: 8W, Energy Star Listed, Dimmable, Omni Direction Type, Color Temperature 2700K

Certification

UL/cUL Listed



LED Type

Model	Input Voltage	Input Wattage	Finish	Shade	Dimension (OD x H x H1)	Lamp	Energy Star
P117-A-62	120V	8W	Satin Nickel	Clear Glass	4.8" x 9.8" x 42.0"	E26 Filament Type LED Bulb, 8W, 2700K	---

Note: H1- Total Height