



## DETAILS

Material: STEEL

## LAMPING

Light Source: Both

Bulb Included: No

Bulb Type: Candelabra Base

Bulb Quantity: 3

Watts per Bulb: 60

## ELECTRICAL

Dimmable: Yes

Voltage: 120v

Wire Length: 12'

## INSTALLATION

Location Rating: Damp

Install Position: N/A

Sloped Ceiling Compatible: Yes

## DIMENSIONS

Dimensions: 10.00" W x 14.25" H x 10.00" D

Overall Height: 115.75'

Canopy Dimensions: 5.00"W x 5.00"D

Chain/Downrod Length: 8'

Weight: 4.11 lbs