



DIMENSIONS

Dimensions: 15.75" W x 3.00" H x 15.75" D
Canopy Dimensions: 15.00"W x 15.00"D
Weight: 10.78 lbs

DETAILS

Material: STEEL
Glass/Shade Description: Clear Glass Crystal
- Glass - Crystal

LAMPING

Light Source: Integrated LED

ELECTRICAL

Dimmable: Yes
Dimmer Type: ELV
Voltage: 120v
Wire Length: 0.5'

INSTALLATION

Location Rating: Damp
Install Position: N/A
Sloped Ceiling Compatible: Yes

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Inc. Compliance with U.S. COPYRIGHT and PATENT requirements, notification is hereby presented in this form that this literature, or this product depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contray to the best interests of Quoizel Inc. 03/31/2013