

STF8624BN
Stafford Bath
Brushed Nickel



DIMENSIONS

Dimensions: 24.00" W x 9.00" H x 6.75" D
Backplate Dimensions: 5.00"H x 5.00"W
HCWO: 4.75"
Weight: 4.72 lbs

DETAILS

Material: STEEL
Glass/Shade Description: Clear Seedy Glass - Glass - Seeded

LAMPING

Light Source: Both
Bulb Included: No
Bulb Type: Medium Base
Bulb Quantity: 3
Watts per Bulb: 100

ELECTRICAL

Dimmable: Yes
Voltage: 120v
Wire Length: 0.5'

INSTALLATION

Location Rating: Damp
Install Position: Up/Down

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Inc. Compliance with U.S. COPYRIGHT and PATENT requirements, notification is hereby presented in this form that this literature, or this product depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contray to the best interests of Quoizel Inc. 03/31/2013