



## UBOOT40/64-NI-KIT

Ruland UBOOT40/64-NI-KIT, Universal Joint Boot for 2.495" (63.37mm) OD, Nitrile, Quintuple Bellows



### Description

Ruland UBOOT40/64-NI-KIT is a Nitrile boot cover kit for universal joints with an OD of 2.495" or 63.37mm. This boot cover protects the universal joint from unwanted contaminants such as dust and can be packed with grease for lubrication retention. It comes with zip ties that seat into grooves on each yoke ensuring a tight seal. UBOOT40/64-NI-KIT is made from Nitrile for durability and abrasion resistance that helps protect the boot from being damaged and grease leaking out or contaminants entering the joint. Nitrile also has high resistance to petroleum-based oils and fuels, silicone greases, hydraulic fluids, water, and alcohol which are commonly present in operating environments where this universal joint is used. It is designed to fit with single universal joints beginning with US40, USSK40, MUS64, and MUSSK64.

### Product Specifications

<b>Boot Outer Diameter</b>	3.50 in (88.9 mm)	<b>Length (L)</b>	4.000 in (101.6mm)
<b>Bellows</b>	Quintuple	<b>Material Specification</b>	Nitrile
<b>Manufacturer</b>	Belden Universal	<b>Country of Origin</b>	USA
<b>Weight (lbs)</b>	0.179000	<b>UPC</b>	634529289419
<b>Tariff Code</b>	8483.60.4000	<b>UNSPC</b>	25173810
<b>Note 1</b>	Performance ratings are for guidance only. The user must determine suitability for a particular application.		