



UD18-XX-XX-F

Ruland UD18-XX-XX-F, Machinable Bore Double Universal Joint, Friction Bearing, Steel, 1.120" (28.4mm) OD, 5.125" (130.2mm) Length




Description

Ruland UD18-XX-XX-F is a double cardan friction bearing universal joint with plain bores that can be machined to a bore size and geometry of the user's choice. It has a 1.120" (28.4mm) OD and 5.125" (130.2mm) length. UD18-XX-XX-F is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UD18-XX-XX-F is made from high grade alloy steel for durability and high strength. It can be combined with boot UBOOT18/29-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

| | | | |
|--|-----------------------|--------------------------------------|-----------------------------------|
| B1 Max Shaft Penetration | 1.220 in (31.0 mm) | B2 Max Shaft Penetration | 1.220 in (31.0 mm) |
| Joint Outer Diameter (OD) | 1.120 in (28.4 mm) | Length (L) | 5.125 in (130.2 mm) |
| Center Yoke Length (LC) | 1.625 in (41.3 mm) | Yoke Length (LY) | 1.750 in (44.5 mm) |
| Hub Depth (LH) | 1.220 in (31.0 mm) | Max Round Bore (Inch) | 0.625 in |
| Max Round Bore (Metric) | 15 mm | Max Hex or Square Bore (Inch) | 0.6250 in |
| Max Hex or Square Bore (Metric) | 14 mm | Max Blind Bore (Inch) | 0.8750 in |
| Max Blind Bore (Metric) | 22 mm | Max Round Bore w/ Key (Inch) | 5/8" Bore, 3/16" Keyway |
| Max Round Bore w/ Key (Metric) | 16mm Bore, 5mm Keyway | Peak Torque | 2,925 in-lb (330.5 Nm) |
| Rated Torque | 585 in-lb (66.1 Nm) | Max Operating Angle | 90° |
| Material Specification | Alloy Steel | Manufacturer | Belden Universal |
| Country of Origin | USA | Weight (lbs) | 1.175000 |
| Recommended Lubricant | LUBRIPLATE No. 1200-2 | Matching Boot Cover | UBOOT18/29-NI-KIT |
| UPC | 634529288467 | Tariff Code | 8483.60.4000 |
| UNSPC | 25173810 | | |

Note 1 Performance ratings are for guidance only. The user must determine suitability for a particular application.

Prop 65  **WARNING** This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.