



UD20-XX-XX-SS

Ruland UD20-XX-XX-SS, Machinable Bore Double Universal Joint, Friction Bearing, Steel, 1.245" (31.6mm) OD, 5.625" (142.9mm) Length



Description

Ruland UD20-XX-XX-SS is a double cardan friction bearing universal joint with plain bores that can be machined to a bore size and geometry of the user's choice. It has a 1.245" (31.6mm) OD and 5.625" (142.9mm) length. UD20-XX-XX-SS is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UD20-XX-XX-SS is made from high grade stainless steel for increased corrosion resistance. It can be combined with boot UBOOT20/32-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

B1 Max Shaft Penetration	1.250 in (31.8 mm)	B2 Max Shaft Penetration	1.250 in (31.8 mm)
Joint Outer Diameter (OD)	1.245 in (31.6 mm)	Length (L)	5.625 in (142.9 mm)
Center Yoke Length (LC)	1.875 in (47.6 mm)	Yoke Length (LY)	1.875 in (47.6 mm)
Hub Depth (LH)	1.250 in (31.8 mm)	Max Round Bore (Inch)	0.750 in
Max Round Bore (Metric)	19 mm	Max Hex or Square Bore (Inch)	0.7500 in
Max Hex or Square Bore (Metric)	16 mm	Max Blind Bore (Inch)	1.0000 in
Max Blind Bore (Metric)	25 mm	Max Round Bore w/ Key (Inch)	3/4" Bore, 3/16" Keyway
Max Round Bore w/ Key (Metric)	19mm Bore, 6mm Keyway	Peak Torque	3,060 in-lb (345.7 Nm)
Rated Torque	612 in-lb (69.1 Nm)	Max Operating Angle	90°
Material Specification	Yokes: 303 Stainless Steel Pins and Blocks: 416 Stainless Steel	Manufacturer	Belden Universal
Country of Origin	USA	Weight (lbs)	1.597000
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT20/32-NI-KIT
UPC	634529288542	Tariff Code	8483.60.4000
UNSPC	25173810		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠️ WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		