




UD24-XX-XX-SS-KIT

Ruland UD24-XX-XX-SS-KIT, Machinable Bore Double Universal Joint Kit, Friction Bearing, Stainless Steel, 1.495" (38.0mm) OD, 6.563" (166.7mm) Length



Description

Ruland UD24-XX-XX-SS-KIT is a double cardan friction bearing universal joint kit that can be machined with a bore size and geometry of the user's choice. It has a 1.495" (38.0mm) OD and 6.563" (166.7mm) length. UD24-XX-XX-SS-KIT is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UD24-XX-XX-SS-KIT is made from high grade stainless steel for increased corrosion resistance. It can be combined with boot UBOOT24/38-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

B1 Max Shaft Penetration	1.400 in (35.6 mm)	B2 Max Shaft Penetration	1.400 in (35.6 mm)
Joint Outer Diameter (OD)	1.495 in (38.0 mm)	Length (L)	6.563 in (166.7 mm)
Center Yoke Length (LC)	2.313 in (58.8 mm)	Yoke Length (LY)	2.125 in (54.0 mm)
Hub Depth (LH)	1.400 in (35.6 mm)	Max Round Bore (Inch)	0.875 in
Max Round Bore (Metric)	22 mm	Max Hex or Square Bore (Inch)	0.7500 in
Max Hex or Square Bore (Metric)	20 mm	Max Blind Bore (Inch)	1.2500 in
Max Blind Bore (Metric)	31 mm	Max Round Bore w/ Key (Inch)	7/8" Bore, 3/16" Keyway
Max Round Bore w/ Key (Metric)	22mm Bore, 6mm Keyway	Peak Torque	6,525 in-lb (737.2 Nm)
Rated Torque	1,305 in-lb (147.4 Nm)	Max Operating Angle	90°
Material Specification	Yokes: 303 Stainless Steel Pins and Blocks: 416 Stainless Steel	Manufacturer	Belden Universal
Country of Origin	USA	Weight (lbs)	2.774000
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT24/38-NI-KIT
UPC	634529288610	Tariff Code	8483.60.4000
UNSPC	25173810		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠️ WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		