



UDSK18-5/8"-14MM-F

Ruland UDSK18-5/8"-14MM-F, 5/8" x 14mm Double Universal Joint, Friction Bearing, Steel, Set Screw With Keyway, 1.120" (28.4mm) OD, 5.125" (130.2mm) Length



Description

Ruland UDSK18-5/8"-14MM-F is a double cardan friction bearing universal joint with 0.6250" x 14mm bores, 3/16" x 5mm keyways, 1.120" (28.4mm) OD, 5.125" (130.2mm) length, and 1/4-20 set screws. It is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UDSK18-5/8"-14MM-F is made from high grade alloy steel for durability and high strength. It can be combined with boot UBOOT18/29-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	0.6250 in	Small Bore (B2)	14 mm
Keyway (K1)	3/16 in	Keyway (K2)	5 mm
B1 Max Shaft Penetration	1.220 in (31.0 mm)	B2 Max Shaft Penetration	1.220 in (31.0 mm)
Joint Outer Diameter (OD)	1.120 in (28.4 mm)	Bore Tolerance	+0.0010 in / -0.0000 in (+0.025 mm / -0.000 mm)
Length (L)	5.125 in (130.2 mm)	Center Yoke Length (LC)	1.625 in (41.3 mm)
Yoke Length (LY)	1.750 in (44.5 mm)	Hub Depth (LH)	1.220 in (31.0 mm)
Broached Set Screw	1/4-20	Screw Finish	Black Oxide
Peak Torque	2,925 in-lb (330.5 Nm)	Rated Torque	585 in-lb (66.1 Nm)
Max Operating Angle	90°	Material Specification	Alloy Steel
Manufacturer	Belden Universal	Country of Origin	USA
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT18/29-NI-KIT
UPC	63452932455	Tariff Code	8483.60.4000
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠️ WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .		