



UDSK28-1"-20MM-SS

Ruland UDSK28-1"-20MM-SS, 1" x 20mm Double Universal Joint, Friction Bearing, Stainless Steel, Set Screw With Keyway, 1.745" (44.3mm) OD, 7.750" (196.9mm) Length



Description

Ruland UDSK28-1"-20MM-SS is a double cardan friction bearing universal joint with 1.0000" x 20mm bores, 1/4" x 6mm keyways, 1.745" (44.3mm) OD, 7.750" (196.9mm) length, and 5/16-18 set screws. It is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UDSK28-1"-20MM-SS is made from high grade stainless steel for increased corrosion resistance. It can be combined with boot UBOOT28/44-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	1.0000 in	Small Bore (B2)	20 mm
Keyway (K1)	1/4 in	Keyway (K2)	6 mm
B1 Max Shaft Penetration	1.610 in (40.9 mm)	B2 Max Shaft Penetration	1.610 in (40.9 mm)
Joint Outer Diameter (OD)	1.745 in (44.3 mm)	Bore Tolerance	+0.0010 in / -0.0000 in (+0.025 mm / -0.000 mm)
Length (L)	7.750 in (196.9 mm)	Center Yoke Length (LC)	2.750 in (69.9 mm)
Yoke Length (LY)	2.500 in (63.5 mm)	Hub Depth (LH)	1.610 in (40.9 mm)
Broached Set Screw	5/16-18	Screw Finish	Bright
Peak Torque	9,450 in-lb (1,067.7 Nm)	Rated Torque	1,890 in-lb (213.5 Nm)
Max Operating Angle	90°	Material Specification	Yokes: 303 Stainless Steel Pins and Blocks: 416 Stainless Steel
Manufacturer	Belden Universal	Country of Origin	USA
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT28/44-NI-KIT
UPC	63452932682	Tariff Code	8483.60.4000
UNSPC	25173810		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠️ WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		