



US32-1 3/16"-20MM-F

Ruland US32-1 3/16"-20MM-F, 1 3/16" x 20mm Single Universal Joint, Friction Bearing, Steel, 1.995" (50.7mm) OD, 5.500" (139.7mm) Length



Description

Ruland US32-1 3/16"-20MM-F is a single cardan friction bearing universal joint with 1.1875" x 20mm bores, 1.995" (50.7mm) OD, and 5.500" (139.7mm) length. It is ideal for applications with space constraints and has higher torque capacity than equivalently sized double universal joints. This plain bearing universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 45° when compared to commodity style single universal joints. US32-1 3/16"-20MM-F is made from high grade alloy steel for durability and high strength. It can be combined with boot UBOOT32/51-NI-KIT to protect the joint from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This single cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

| | | | |
|----------------------------------|--|---------------------------------|---|
| Bore (B1) | 1.1875 in | Small Bore (B2) | 20 mm |
| B1 Max Shaft Penetration | 1.700 in (43.2 mm) | B2 Max Shaft Penetration | 1.700 in (43.2 mm) |
| Joint Outer Diameter (OD) | 1.995 in (50.7 mm) | Bore Tolerance | +0.0010 in / -0.0000 in (+0.025 mm / -0.000 mm) |
| Length (L) | 5.500 in (139.7 mm) | Yoke Length (LY) | 2.750 in (69.9 mm) |
| Hub Depth (LH) | 1.700 in (43.2 mm) | Peak Torque | 21,500 in-lb (2,429.2 Nm) |
| Rated Torque | 4,300 in-lb (485.8 Nm) | Max Operating Angle | 45° |
| Material Specification | Alloy Steel | Manufacturer | Belden Universal |
| Country of Origin | USA | Recommended Lubricant | LUBRIPLATE No. 1200-2 |
| Matching Boot Cover | UBOOT32/51-NI-KIT | UPC | 63452933411 |
| Tariff Code | 8483.60.4000 | UNSPC | 25173810 |
| Note 1 | Performance ratings are for guidance only. The user must determine suitability for a particular application. | | |
| Prop 65 | ⚠️ WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov . | | |