




## US8-XX-XX-F-KIT

Ruland US8-XX-XX-F-KIT, Machinable Bore Single Universal Joint Kit, Friction Bearing, Steel, 0.495" (12.6mm) OD, 2.000" (50.8mm) Length




### Description

Ruland US8-XX-XX-F-KIT is a single cardan friction bearing universal joint kit that can be machined with a bore size and geometry of the user's choice. It has a 0.495" (12.6mm) OD and 2.000" (50.8mm) length. US8-XX-XX-F-KIT is ideal for applications with space constraints and has higher torque capacity than equivalently sized double universal joints. This plain bearing universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 45° when compared to commodity style single universal joints. US8-XX-XX-F-KIT is made from high grade alloy steel for durability and high strength. It can be combined with boot UBOOT8/13-NI-KIT to protect the joint from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This single cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

### Product Specifications

|                                      |                                  |                                        |                       |
|--------------------------------------|----------------------------------|----------------------------------------|-----------------------|
| <b>B1 Max Shaft Penetration</b>      | 0.740 in (18.8 mm)               | <b>B2 Max Shaft Penetration</b>        | 0.740 in (18.8 mm)    |
| <b>Joint Outer Diameter (OD)</b>     | 0.495 in (12.6 mm)               | <b>Length (L)</b>                      | 2.000 in (50.8 mm)    |
| <b>Yoke Length (LY)</b>              | 1.000 in (25.4 mm)               | <b>Hub Depth (LH)</b>                  | 0.740 in (18.8 mm)    |
| <b>Max Round Bore (Inch)</b>         | 0.2813 in                        | <b>Max Round Bore (Metric)</b>         | 7 mm                  |
| <b>Max Hex or Square Bore (Inch)</b> | 0.2813 in                        | <b>Max Hex or Square Bore (Metric)</b> | 7 mm                  |
| <b>Max Blind Bore (Inch)</b>         | 0.3750 in                        | <b>Max Blind Bore (Metric)</b>         | 9 mm                  |
| <b>Peak Torque</b>                   | 350 in-lb (39.5 Nm)              | <b>Rated Torque</b>                    | 70 in-lb (7.9 Nm)     |
| <b>Max Operating Angle</b>           | 45°                              | <b>Material Specification</b>          | Alloy Steel           |
| <b>Manufacturer</b>                  | Belden Universal                 | <b>Country of Origin</b>               | USA                   |
| <b>Weight (lbs)</b>                  | 0.094000                         | <b>Recommended Lubricant</b>           | LUBRIPLATE No. 1200-2 |
| <b>Matching Boot Cover</b>           | <a href="#">UBOOT8/13-NI-KIT</a> | <b>UPC</b>                             | 634529290255          |
| <b>Tariff Code</b>                   | 8483.60.4000                     | <b>UNSPC</b>                           | 25173810              |

**Note 1** Performance ratings are for guidance only. The user must determine suitability for a particular application.

**Prop 65**  **WARNING** This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).