

# USHB

## TECHNICAL SPECIFICATIONS:

- :: Housing: Aluminum heat sink, White finish
- :: Voltage: 120-277V AC; 60Hz AC
- :: Cord type: 6' SJTW 18/3 AWG cable
- :: Efficacy: 130LM/W
- :: CRI: >80
- :: Power Factor: ≥0.9
- :: Beam Angle: 110°
- :: THD: <20%
- :: 0~10V Dimming
- :: Operating Temp.: -4°F to 122°F
- :: Aluminum LED Board: High conductive, waterproof, aging resistant, salt mist resistance, long-life
- :: 5-year warranty
- :: Suitable for Wet Locations, IP66



Bottom View



B1

## LED SATURN HIGH BAY

CATALOG NO.	WATTS	LUMENS	COLOR TEMP	DIMENSIONS
USHB-100W-50K	100W	13000LM	5000K	17.52" (Diameter) x 7.47" (H)
USHB-100W-40K	100W	13000LM	4000K	
USHB-150W-50K	150W	19500LM	5000K	
USHB-150W-40K	150W	19500LM	4000K	
USHB-200W-50K	200W	26000LM	5000K	
USHB-200W-40K	200W	26000LM	4000K	
USHB-240W-50K	240W	31200LM	5000K	
USHB-240W-40K	240W	31200LM	4000K	