IL-1326W

Protect and preserve important documents with the Royal Sovereign 13”, 2 Roller Pouch Laminator.



Highlights

- **Efficiency:** Laminates at 18.90 in. (480 mm.) per minute.
- **Protection:** 2 roller system prevents wrinkling, bubbling, and hazing.
- **Versatile:** Hot and Cold lamination for pouches 3-5 Mil. thick.
- **Convenience:** 60 second warmup time.
- **Jam Assistance**: Jam removal button located on the back of the unit.
- **Overheat Protection:** After 30 minutes of non-use the heater will shut off.

Perfect solution for home, office, or professional lamination!

IL-1326W

13” ENTRY FEED

GLASS TOP DESIGN

60 SECOND WARMUP



SPECIFICATIONS

Power Supply Voltage	120V (60 Hz)
Power Consumption	760W
Number of Rollers	2
Speed	18.9 in. (480 mm.) per minute
Maximum Entry Width	13 in. (330 mm.)
Pouch Mil. Thickness	3 Mil. – 5 Mil.
Warm-up Time	60 seconds
Certification	cTUVus
Dimensions	17.1” x 4.13” x 2.95” 435 mm x 105 mm x 75 mm
Weight	3.88 lbs. (1.76 kg)

Individual Carton Dimensions	18.3”W x 5.2”D x 3.74”H 465 mm x 132 mm x 95 mm
Individual Carton Weight	4.54 lbs. / 2.06 kgs
Individual Carton UPC Code	849023090281
Master Carton Dimensions	18.78”W x 15.67”D x 5.98”H 477 mm x 398 mm x 152 mm
Master Carton Weight	19.07 lbs. / 8.65 kgs
Master Carton Count	4
Master Carton UPC Code	50849023090286

1 Year Warranty