



ELEMENT SPECS		
PART NUMBER	850S	
MATERIAL	WIREMESH	
FLOW RATE	290 CFM	493 m ³ /hr
SURFACE AREA	4.5 ft ²	0.4 m ²
I.D.	3.50"	89mm
O.D.	5.88"	149mm
HEIGHT	8.58"	218mm