

Project Name

Location

Prepared By

NUVO 60-7493

COLONY 1 LIGHT MEDIUM FLUSH

Notes

[www] 11-25-2021 04:01:30

General

Status	Active
Collection	Colony
Finish	Matte White / Burnished Brass
Style	Mid-Century Modern
Number of Lamps	1
Height (in.)	7.000
Width (in.)	19.875
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Weight (lb.)	7.64
Sloped Ceiling	No
Up/Down Installation	Down Only
Fixture Type	Flush Mount
Fixture Material	Iron

Dimensions

Back Plate or Canopy Length (in.)	5.750
Back Plate or Canopy Width (in.)	5.750
Back Plate or Canopy Height (in.)	1.125
Wire Quantity	1

Compliance

Safety Listing	cULus
Location Rating	Dry
Energy Star	No
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------