

Project Name

Location

Prepared By

## NUVO 60-7494

COLONY 1 LIGHT MEDIUM FLUSH

Notes

[www] 11-29-2021 04:01:39

**General**

Status	Active
Collection	Colony
Finish	Matte Black / Burnished Brass
Style	Mid-Century Modern
Number of Lamps	1
Height (in.)	7.000
Width (in.)	19.875
Indoor or Outdoor Fixture	Indoor

**Specifications**

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Weight (lb.)	7.64
Sloped Ceiling	No
Up/Down Installation	Down Only
Fixture Type	Flush Mount
Fixture Material	Iron

**Dimensions**

Back Plate or Canopy Length (in.)	5.750
Back Plate or Canopy Width (in.)	5.750
Back Plate or Canopy Height (in.)	1.125
Wire Quantity	1

**Compliance**

Safety Listing	cULus
Location Rating	Dry
Energy Star	No
California Prop 65	Lead

**Additional Information**

Warranty	1 Year Limited - Fixtures
----------	---------------------------