

Project Name

Location

Prepared By

NUVO 60-7540

HOMESTEAD 1 LT SM WALL LANTERN

Notes

[www] 11-25-2021 04:01:39

General

Status	Active
Collection	Homestead
Finish	Black / Wood
Style	Rustic Industrial
Number of Lamps	1
Height (in.)	10.625
Width (in.)	5.375
Extension (in.)	6.000
Indoor or Outdoor Fixture	Outdoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear Seeded
Weight (lb.)	4.39
Up/Down Installation	Down Only
Fixture Type	Wall Lantern
Fixture Material	Aluminum / Iron / Glass

Dimensions

Back Plate or Canopy Length (in.)	6.300
Back Plate or Canopy Width (in.)	5.120
Back Plate or Canopy Height (in.)	0.870

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	No
ADA Compliant	No
California Prop 65	Lead
RoHS Compliant	No
FCC Compliant	No

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------