

Project Name

Location

Prepared By

NUVO 60-7631

INTERSECTION 1LT VANITY

Notes

[www] 11-29-2021 04:01:39

General

Status	Active
Collection	Intersection
Finish	Polished Nickel
Style	Industrial Chic
Number of Lamps	1
Height (in.)	8.500
Width (in.)	4.500
Extension (in.)	5.375
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear
Weight (lb.)	2.18
Sloped Ceiling	No
Up/Down Installation	Up/Down
Fixture Type	Vanity
Fixture Material	Iron / Glass

Dimensions

Back Plate or Canopy Length (in.)	4.500
Back Plate or Canopy Width (in.)	4.500
Back Plate or Canopy Height (in.)	0.750
Wire Quantity	1

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------