

Project Name

Location

Prepared By



NUVO 60-7691

HALTER 4LT PENDANT

Notes

[www] 05-06-2023 01:09:30

General

Status	Active
Collection	Halter
Finish	Natural Brass
Style	Transitional
Number of Lamps	4
Height (in.)	21.625
Width (in.)	22.625
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Fabric Description	White Linen
Weight (lb.)	6.05
Sloped Ceiling	Yes
Fixture Type	Pendant
Fixture Material	Steel

Dimensions

Back Plate or Canopy Height (in.)	0.87
Back Plate or Canopy Diameter (in.)	5.04
Stem Length	36 in.

Compliance

Safety Listing	cULus
Location Rating	Damp
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead

Additional Information

Includes	(2) 6 inch and (2) 12 inch rods
Warranty	1 Year Limited - Fixtures