

Project Name

Location

Prepared By



NUVO 60-7740

COLBY 1 LIGHT WALL SCONCE

Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Colby
Finish	Matte Black
Style	Transitional
Number of Lamps	1
Height (in.)	24.00
Width (in.)	8.13
Extension (in.)	6.00
Indoor or Outdoor Fixture	Indoor

Specifications

Base	G9 Double Loop
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Frost
Weight (lb.)	2.86
Fixture Shape	Linear
Fixture Type	Wall Sconce
Fixture Material	Steel

Dimensions

Back Plate or Canopy Diameter (in.)	4.75
Top to Outlet	6.50

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------