

Project Name

Location

Prepared By



## NUVO 60-7742

COLBY 1 LIGHT WALL SCONCE

### Notes

[www] 07-05-2023 01:10:03

### General

|                           |               |
|---------------------------|---------------|
| Status                    | Active        |
| Collection                | Colby         |
| Finish                    | Natural Brass |
| Style                     | Transitional  |
| Number of Lamps           | 1             |
| Height (in.)              | 24.00         |
| Width (in.)               | 8.13          |
| Extension (in.)           | 6.00          |
| Indoor or Outdoor Fixture | Indoor        |

### Specifications

|                   |                |
|-------------------|----------------|
| Base              | G9 Double Loop |
| Bulb Type         | Incandescent   |
| Max Wattage       | 60W            |
| Bulb Included     | No             |
| Glass Description | Frost          |
| Weight (lb.)      | 2.86           |
| Fixture Shape     | Linear         |
| Fixture Type      | Wall Sconce    |
| Fixture Material  | Steel          |

### Dimensions

|                                     |      |
|-------------------------------------|------|
| Back Plate or Canopy Diameter (in.) | 4.75 |
| Top to Outlet                       | 6.50 |

### Compliance

|                    |                |
|--------------------|----------------|
| Safety Listing     | cULus - Listed |
| Location Rating    | Damp           |
| Energy Star        | No             |
| DLC Approved       | No             |
| California Prop 65 | Lead           |

### Additional Information

|          |                           |
|----------|---------------------------|
| Warranty | 1 Year Limited - Fixtures |
|----------|---------------------------|