

Project Name

Location

Prepared By



NUVO 60-7747

TERRACE 1 LIGHT WALL SCONCE

Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Terrace
Finish	Polished Nickel
Style	Contemporary
Number of Lamps	1
Height (in.)	24.00
Width (in.)	4.50
Extension (in.)	5.63
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Crackle
Weight (lb.)	3.30
Up/Down Installation	Up or Down
Fixture Shape	Linear
Fixture Type	Wall Sconce
Fixture Material	Steel

Dimensions

Back Plate or Canopy Width (in.)	4.50
Back Plate or Canopy Height (in.)	4.50
Top to Outlet	11.75

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------